

|                |
|----------------|
| 760 - 830 nm   |
| 830 - 920 nm   |
| 920 - 1100 nm  |
| 1100 - 1300 nm |
| 1300 - 1450 nm |
| 1450 - 1650 nm |
| 1650 - 1850 nm |
| 1850 - 1900 nm |
| 1900 - 2200 nm |
| 2200 - 2600 nm |
| 2600 - 3000 nm |
| 3000 - 6000 nm |

# DFB laser diodes from 760 nm to 830 nm


## nanoplus single mode laser diodes

nanoplus is the only manufacturer worldwide routinely providing single and multi mode lasers at any wavelength from 760 to 6000 nm. At wavelengths up to 14  $\mu\text{m}$ , QCLs complete nanoplus' laser portfolio. Our patented distributed feedback laser diodes deliver single mode emission with well defined optical properties enabling a wide range of applications.

nanoplus lasers operate reliably in tens of thousands of installations worldwide, including chemical and metallurgical industries, gas pipelines, power plants, medical systems, airborne and satellite applications.

### key features

- ✓ very high spectral purity
- ✓ narrow linewidth
- ✓ excellent reliability
- ✓ wide variety of packaging options
- ✓ customer-specific designs available



### application areas

- ✓ high performance gas sensing for process and environmental control
- ✓ precision metrology
- ✓ atomic clocks
- ✓ spectroscopy
- ✓ space technology

nanoplus lasers with excellent performance are specifically designed and characterized to fit your needs. This data sheet summarizes typical properties of nanoplus DFB lasers in the range from 760 nm to 830 nm. Overleaf data for lasers used for high performance O<sub>2</sub> sensing are given as an example.

| general ratings (T = 25 °C)        | symbol           | unit | typical |
|------------------------------------|------------------|------|---------|
| optical output power               | P <sub>out</sub> | mW   | 5       |
| reverse voltage                    | V <sub>r</sub>   | V    | 3       |
| forward current                    | I <sub>f</sub>   | mA   | 30      |
| side mode suppression ratio (SMSR) |                  | dB   | > 32    |

On request, lasers with specifically optimized properties, e. g. higher output power, are available.

### laser packaging options

- TO5.6 header with or without cap
- TO5 header with TEC and NTC
- butterfly housing with SM or PM fiber

For dimensions and accessories, please see [www.nanoplus.com](http://www.nanoplus.com)  
 Further packaging options available on request.

device protected by  
 US patent 6.671.306  
 US patent 6.846.689  
 EU patent EP0984535

nanoplus  
 Nanosystems and Technologies GmbH  
 Oberer Kirschberg 4  
 D-97218 Gerbrunn


phone: +49 (0) 931 90827-0  
 fax: +49 (0) 931 90827-19  
 email: sales@nanoplus.com  
 internet: www.nanoplus.com

© copyright nanoplus GmbH 2013, all rights reserved.  
 nanoplus GmbH reserves the right to modify these specifications at any time without notice and is not liable for errors.




# nanoplus DFB laser diodes at 760 nm

A wide variety of gas molecules exhibit characteristic absorption lines in the near infrared. At about 760 nm for example, there is a strong absorption line of O<sub>2</sub>, which can be used for laser based sensing with very high sensitivity. This data sheet reports performance data of laterally and longitudinally single mode nanoplus DFB lasers at this wavelength. Similar performance data are obtained in the entire wavelength range from 760 nm to 830 nm. For examples of performance data of nanoplus lasers in other wavelength ranges, please see [www.nanoplus.com](http://www.nanoplus.com) or contact [sales@nanoplus.com](mailto:sales@nanoplus.com)



*Fig. 1*  
Room temperature cw spectrum of a nanoplus DFB laser diode operating at 760 nm

In many applications, temperature and / or current variations are used to adjust the laser emission precisely to the target wavelength, here on and off the O<sub>2</sub> absorption.



*Fig. 2*  
Mode hop free tuning of a nanoplus 760 nm DFB laser diode by current variation at different temperatures

| electrooptical characteristics (T = 25 °C) | symbol    | unit                             | min       | typ     | max     |
|--|-----------|----------------------------------|-----------|---------|---------|
| peak wavelength                            | $\lambda$ | nm                               | 759       | 760     | 761     |
| threshold current                          | $I_{th}$  | mA                               | 10        | 15      | 30      |
| slope efficiency                           | e         | mW / mA                          | 0.2       | 0.5     | 0.6     |
| temperature tuning coefficient             | $C_T$     | nm / K                           | 0.03      | 0.04    | 0.05    |
| current tuning coefficient                 | $C_I$     | nm / mA                          | 0.010     | 0.020   | 0.025   |
| slow axis (FWHM)                           |           | degrees                          | 30        | 35      | 40      |
| fast axis (FWHM)                           |           | degrees                          | 50        | 60      | 65      |
| emitting area                              | W x H     | $\mu\text{m} \times \mu\text{m}$ | 1.2 x 1.3 | 1.5 x 2 | 2 x 2.2 |
| storage temperatures                       | $T_S$     | °C                               | - 40      | + 20    | + 80    |
| operational temperature at case            | $T_C$     | °C                               | - 20      | + 25    | + 50    |

We will be happy to answer further questions. Please contact us at [sales@nanoplus.com](mailto:sales@nanoplus.com)

